

METALLURGICAL MICROSCOPE



- Infinite optical system, polarization observation, dark field observation
- Kohler illumination system provides uniform illumination field
- Objectives 50X, 100X are spring type

SPECIFICATION

Code	5103-M100	5103-M1000**(bright field objectives)			5103-M1000BD**(bright & dark field objectives)			
Illumination	6V/30W ha	6V/30W halogen lamp, brightness is adjustable			12V/50W halogen lamp, brightness is adjustable			
Objective	bright field objectives				bright & dark field objectives			
(infinite plan achromatic)	10X	20X	50X	100X	5X	10X	20X	50X
Working distance	20.2mm	8.80mm	3.68mm	0.40mm	9.70mm	9.30mm	7.23mm	2.50mm
Numerical aperture	0.25	0.40	0.70	0.85	0.12	0.25	0.40	0.70
Magnification	100X~1000	100X~1000X			50X~500X			
Eyepiece (wide field)	10X (view field: Ø22mm)							
	double layer							
Stage	size: 242×200mm							
	travel: 30x30mm							
Pupil distance	53~75mm	53~75mm						
Diopter adjustment	±5 diopter	±5 diopter (one eyepiece)						
Power supply	220V, 50/6	220V, 50/60Hz **						
Dimension (L×W×H)	614×250×3	614×250×394mm						
Weight	13kg							

STANDARD DELIVERY

CIAIDARD DELIVER			
Main unit	1 pc		
Polarizer and analyzer	1 pc of each		
Anti-dust cover	1 pc		

OPTIONAL ACCESSORY

of Honal Additional				
	PL40X	5101-M-BD40X		
Bright & dark field objective (for 5103-M1000BD)	PL60X	5101-M-BD60X		
	PL80X	5101-M-BD80X		
	PL100X	5101-M-BD100X		
10X dividing eyepiece (0.1m	5103-M-EPD10X			
Camera adapter	5101-M-ADAPTER			

Bright field objective (for 5103-M1000)	PL5X	5101-M-OB5X
	PL40X	5101-M-OB40X
	PL60X	5101-M-OB60X
	PL80X	5101-M-OB80X

^{**}Add "-U" on code No. when power supply is 110V, 50/60Hz